



22 Ponderosa Ct

P.O. Box 1468

Montrose, CO 81401

www.galiso.com (800)854-3789



95CFM

Galiso P/N 25-51-3184 GCD-110v/220v



Fast, Efficient, Low Cost, Ideal for Medical D & E's, SCBA's, Scuba and small CO² Cylinders

- Drain, invert, and place up to 4 cylinders on the drier probes.
- Cylinders are properly dried in a matter of minutes, ready to be inspected and placed back into service
- The built-in drier motor is quiet, production temperatures to 175° to accelerate the drying of steel and aluminum cylinders.
- Select the "cool" setting to protect fiber wrapped or composite cylinder. Cool temp is between 115° and 135°

Dimensions.....59"L x 21" W x 28"H
 Capacity..... Up to 4 10" x 30" Cylinders
 Electrical.....110v, 60Hz or 220v, 60Hz

Galiso P/N 25-51-3183 GCD220v 1phase only

UP to 160 CFM